

URC Attachment Kit



FEATURES

Attaches cable brace to structure

Two-way bracing kit with oval sleeves

Wraps around structural steel members

Material: Steel
Finish: Electrogalvanized; Painted



SPECIFICATIONS

Catalog Number	Brace Size	Color	Hole Size	Brace Length	Cable Length	UL Listed Load
CSB2W12URC12L10	#12	Red	9/16"	10'	14'	418lb
CSB2W12URC38L10	#12	Red	7/16"	10'	14'	418lb
CSB2W18URC12L10	#18	White	9/16"	10'	14'	772lb
CSB2W18URC38L10	#18	White	7/16"	10'	14'	772lb
CSB2W36URC12L10	#36	Blue	9/16"	10'	14'	1909lb
CSB2W36URC58L10	#36	Blue	11/16"	10'	14'	1909lb

ADDITIONAL PRODUCT DETAILS

FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® piping systems and products made with TempRite® Technology.™ "The FBC System Compatible Logo, FBC™, FlowGuard Gold®, BlazeMaster®, Corzan®, and TempRite® are trademarks of Lubrizol Advanced Materials, Inc. or its affiliates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

