

Wire Basket Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY Wire Basket Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY Wire Basket Tray Ground Splice and nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT12	Electrogalvanized		0.62"	1.63"	15.292"	0.531"
WBTCLSPRT12BA	Electrogalvanized	Black	0.62"	1.63"	15.292"	0.531"
WBTCLSPRT12WH	Electrogalvanized	White	0.62"	1.63"	15.292"	0.531"
WBTCLSPRT16	Pregalvanized		0.62"	1.63"	19.229"	0.531"
WBTCLSPRT16BA	Pregalvanized	Black	0.62"	1.63"	19.229"	0.531"

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT16WH	Pregalvanized	White	0.62"	1.63"	19.229"	0.531"
WBTCLSPRT18	Electrogalvanized		0.62"	1.63"	21.198"	0.531"
WBTCLSPRT18BA	Electrogalvanized	Black	0.62"	1.63"	21.198"	0.531"
WBTCLSPRT18WH	Electrogalvanized	White	0.62"	1.63"	21.198"	0.531"
WBTCLSPRT20	Pregalvanized		0.62"	1.63"	23.167"	0.531"
WBTCLSPRT20BA	Pregalvanized	Black	0.62"	1.63"	23.167"	0.531"
WBTCLSPRT20WH	Pregalvanized	White	0.62"	1.63"	23.167"	0.531"
WBTCLSPRT24	Electrogalvanized		0.62"	1.63"	27.104"	0.531"
WBTCLSPRT24BA	Electrogalvanized	Black	0.62"	1.63"	27.104"	0.531"
WBTCLSPRT24WH	Electrogalvanized	White	0.62"	1.63"	27.104"	0.531"
WBTCLSPRT6	Pregalvanized		0.62"	1.63"	9.386"	0.531"
WBTCLSPRT6BA	Pregalvanized	Black	0.62"	1.63"	9.386"	0.531"
WBTCLSPRT6WH	Pregalvanized	White	0.62"	1.63"	9.386"	0.531"
WBTCLSPRT8	Pregalvanized		0.62"	1.63"	11.354"	0.531"
WBTCLSPRT8BA	Pregalvanized	Black	0.62"	1.63"	11.354"	0.531"

Table 2/2

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT8WH	Pregalvanized	White	0.62"	1.63"	11.354"	0.531"

Table 1/2


Catalog Number	Unit Weight	Certifications
WBTCLSPRT12	1.1 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT12BA	1.1 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT12WH	1.1 lb	
WBTCLSPRT16	1.5 lb	
WBTCLSPRT16BA	1.5 lb	
WBTCLSPRT16WH	1.5 lb	
WBTCLSPRT18	1.6 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT18BA	1.6 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT18WH	1.6 lb	
WBTCLSPRT20	1.9 lb	
WBTCLSPRT20BA	1.9 lb	
WBTCLSPRT20WH	1.9 lb	
WBTCLSPRT24	1.9 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT24BA	1.9 lb	CE, nVent CADDY Wire Basket Tray System

Catalog Number	Unit Weight	Certifications
WBTCLSPRT24WH	1.9 lb	
WBTCLSPRT6	0.55 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT6BA	0.55 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT6WH	0.55 lb	
WBTCLSPRT8	0.8 lb	CE, nVent CADDY Wire Basket Tray System
WBTCLSPRT8BA	0.8 lb	CE, nVent CADDY Wire Basket Tray System

Table 2/2

Catalog Number	Unit Weight	Certifications
WBTCLSPRT8WH	0.8 lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support	Europe Netherlands: +31 800-0200135 France: +33 800 901 793	Europe Germany: 800 1890272 Other Countries: +31 13 5835404	APAC Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500
---	--	--	--

