


Wire Basket Tray Polymer Insert



The nVent CADDY Wire Basket Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray- providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

FEATURES

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection

Color: Black
Material: Polymer

SPECIFICATIONS

Table 1/2


Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM04BA		3.63"	120"	No	0.009 lb
WBTFORM06BA		5.63"	120"	No	0.014 lb
WBTFORM08BA		7.63"	120"	No	0.018 lb
WBTFORM12BA		11.63"	120"	No	0.027 lb
WBTFORM16BA		15.63"	120"	No	0.036 lb
WBTFORM18BA		17.63"	120"	No	0.041 lb
WBTFORM20BA		19.63"	120"	No	0.045 lb
WBTFORM24BA		23.63"	120"	No	0.054 lb
WBTFORM2X12BA	2"	11.63"	120"	Yes	0.036 lb
WBTFORM2X16BA	2"	15.63"	120"	Yes	0.045 lb
WBTFORM2X18BA	2"	17.63"	120"	Yes	0.05 lb
WBTFORM2X20BA	2"	19.63"	120"	Yes	0.054 lb
WBTFORM2X24BA	2"	23.63"	120"	Yes	0.064 lb
WBTFORM2X4BA	2"	3.63"	120"	Yes	0.018 lb
WBTFORM2X6BA	2"	5.63"	120"	Yes	0.023 lb

Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM2X8BA	2"	7.63"	120"	Yes	0.027 lb
WBTFORM4X12BA	4"	11.63"	120"	Yes	0.045 lb
WBTFORM4X16BA	4"	15.63"	120"	Yes	0.054 lb
WBTFORM4X18BA	4"	17.63"	120"	Yes	0.059 lb
WBTFORM4X20BA	4"	19.63"	120"	Yes	0.064 lb

Table 2/2

Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM4X24BA	4"	23.63"	120"	Yes	0.073 lb
WBTFORM4X4BA	4"	3.63"	120"	Yes	0.027 lb
WBTFORM4X6BA	4"	5.63"	120"	Yes	0.032 lb
WBTFORM4X8BA	4"	7.63"	120"	Yes	0.036 lb
WBTFORM6X12BA	6"	11.63"	120"	Yes	0.054 lb
WBTFORM6X16BA	6"	15.63"	120"	Yes	0.064 lb
WBTFORM6X18BA	6"	17.63"	120"	Yes	0.073 lb
WBTFORM6X20BA	6"	19.63"	120"	Yes	0.082 lb
WBTFORM6X24BA	6"	23.63"	120"	Yes	0.082 lb
WBTFORM6X8BA	6"	7.63"	120"	Yes	0.045 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

