


Wire Basket Tray Polymer Insert, Perforated



The nVent CADDY Wire Basket Tray Polymer Insert, Perforated is a precut tray insert designed to protect high-performance cables. The flame-retardant polymer material ensures the safety of critical systems in demanding environments such as data centers and hospitals.

This cable management solution comes in a precut roll to maximize efficiency and allow installers to cut-to-length for greater customization. The precut perforations also ensure easy cable routing and additional securement options with the nVent CADDY Self-Cutting Cable Tie. With quick and precise installations, nVent CADDY helps contractors spend less time on the ladder, and more on finishing the project.

FEATURES

Polymer insert rolls easily into the tray bottom

Designed for commercial and data center applications


Can be easily configured while in the field

Multiple color options to coordinate with cable tray selection

Color:	Black
Material:	Polyvinylchloride
Sides Included:	No
Complies With:	UL® 94V-0

SPECIFICATIONS

Catalog Number	Height (H)	Width (W)	Length (L)	Unit Weight
WBTPERFPOLY18	0.018"	18"	1200.78"	14.33 lb
WBTPERFPOLY24	0.018"	24"	1200.78"	17.417 lb
WBTPERFPOLY8	0.018"	8"	1200.78"	5.95 lb
WBTPERFPOLY30	0.018"	30"	1200.78"	0.0022 lb
WBTPERFPOLY36	0.018"	36"	1200.78"	0.0022 lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

