


Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Steel
Finish: Pregalvanized; Polyurethane



SPECIFICATIONS

Table 1/2


Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTI2X12		2"	28"	28"	3/4"	3.726"
WBTI2X12BA	Black	2"	28"	28"	3/4"	3.726"
WBTI2X12WH	White	2"	28"	28"	3/4"	3.726"
WBTI2X16BA	Black	2"	32"	32"	3/4"	3.726"
WBTI2X18		2"	33.9"	33.9"	3/4"	3.726"
WBTI2X18BA	Black	2"	33.9"	33.9"	3/4"	3.726"
WBTI2X20		2"	35.9"	35.9"	3/4"	3.726"
WBTI2X20BA	Black	2"	35.9"	35.9"	3/4"	3.726"
WBTI2X24		2"	40"	40"	3/4"	3.726"

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTI2X24BA	Black	2"	40"	40"	3/4"	3.726"
WBTI2X24WH	White	2"	40"	40"	3/4"	3.726"
WBTI2X4		2"	20.12"	20.12"		3.726"
WBTI2X4BA	Black	2"	20.12"	20.12"		3.726"
WBTI2X4WH	White	2"	20.12"	20.12"		3.726"
WBTI2X6		2"	22.1"	22.1"		3.726"
WBTI2X6BA	Black	2"	22.1"	22.1"		3.726"
WBTI2X8		2"	24.1"	24.1"		3.726"
WBTI2X8BA	Black	2"	24.1"	24.1"		3.726"
WBTI2X8WH	White	2"	24.1"	24.1"		3.726"

Table 2/2

Catalog Number	Unit Weight	Certifications
WBTI2X12	1.44 lb	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X12BA	1.44 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X12WH	1.44 lb	
WBTI2X16BA	2.057 lb	
WBTI2X18	2.469 lb	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X18BA	2.469 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X20	2.88 lb	UL, cUL
WBTI2X20BA	2.88 lb	
WBTI2X24	3.704 lb	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X24BA	3.704 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X24WH	3.704 lb	
WBTI2X4	0.411 lb	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X4BA	0.411 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X4WH	0.411 lb	
WBTI2X6	0.617 lb	cUL, CE, nVent CADDY Wire Basket Tray System, UL
WBTI2X6BA	0.617 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X8	1.029 lb	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTI2X8BA	1.029 lb	CE, nVent CADDY Wire Basket Tray System
WBTI2X8WH	1.029 lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

