

Cable Clamps, CAC

The cable clamps secures cables into position and relieves any external strains which in turn helps prevent equipment damage.


FEATURES

Description: To secure incoming cables onto the fixing bars CAB and CABP. Holds the cable in position and supports the weight.

Material: Zinc plated steel.

Pack quantity: 25 clamps.

Mounting requirements: Add CAB/CABP to mount the cable clamps CAC.



Material: Mild Steel
Finish: Zinc Plated
Thickness: 14ga

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Enclosure Material	Product Family
CAC0612	CAC0612	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC1014	CAC1014	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC1216	CAC1216	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC1418	CAC1418	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC1822	CAC1822	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC2226	CAC2226	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC2630	CAC2630	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC3034	CAC3034	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC3438	CAC3438	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC3842	CAC3842	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC4246	CAC4246	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing
CAC5864	CAC5864	2.52in	0.98in	0.75in	Mild Steel, Stainless Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.