


Door Switch, DSW



The door switch will allow lights or other electrical devices to turn on, or off, when the enclosure door is opened without the need for any manual interference.

INDUSTRY STANDARDS

CE
cCSAus
CCC

FEATURES

Approvals: CE, cCSAus.

Switch capacity: 3 A / 240 V.

Pack quantity: 1 piece with mounting accessories.

Description: Door switch to activate any electrical device (lighting, signalling, alarms, etc.). Can be mounted after installing the enclosure thereby keeping the door opening free. Fixed on the inside hole pattern of the enclosure's frame in floor standing enclosures. Cable entry M20.

Material: Plastic
Finish: Smooth Matte
Color: Black Gray

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Nominal Voltage	Max Current
DSW01 	DSW01	2.03in	1.57in	2.47in	240V	3A
DSW01QD	DSW01QD	2.03in	1.57in	2.47in	240V	3A

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.