

# Easy Swap Adaptor Plenums for Air Conditioners



When existing air conditioners are damaged or have reached end-of-life, Easy Swap Adaptor Plenums provide a quick and easy means for attaching a new nVent HOFFMAN air conditioners to the cutout left on the enclosure.

## INDUSTRY STANDARDS

Maintains NEMA Type 12 rating when properly installed on a Type 12 enclosure.

NEMA Type 12

IP 54

## FEATURES

No modification of the enclosure required - designed to match the enclosure cut-out and mounting holes of the air conditioner being replaced

Plenum design allows for optimum air flow (vs. a flat plate that can block the air intake and air outtake left by the older air conditioner)

Gasket included

**Color:** Light Gray

**Color Code:** RAL 7035

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Protection Rating | Product Family | Height  | Width   | Depth |
|----------------|----------------|-------------------|----------------|---------|---------|-------|
| PL17N21        | 36416          | NEMA Type 12      | EasySwap       | 20.87in | 12in    | 1.5in |
| PL17N21SS      | 36417          | NEMA Type 12      | EasySwap       | 20.87in | 12in    | 1.5in |
| PLCR23N21      | 36412          | NEMA Type 12      | EasySwap       | 23in    | 10in    | 1.5in |
| PLCR23N21SS    | 36411          | NEMA Type 12      | EasySwap       | 23in    | 10in    | 1.5in |
| PLHC52G57      | 26301          | NEMA Type 12      | EasySwap       | 57.6in  | 22.97in | 1.5in |
| PLHC52T53      | 26302          | NEMA Type 12      | EasySwap       | 52.85in | 23in    | 1.5in |
| PLKG28         | 26582          | NEMA Type 12      | EasySwap       | 36.87in | 19.13in | 1.5in |

| Catalog Number | Article Number | Protection Rating | Product Family | Height  | Width   | Depth  |
|----------------|----------------|-------------------|----------------|---------|---------|--------|
| PLKG52         | 26581          | NEMA Type 12      | EasySwap       | 52.56in | 19.13in | 1.5in  |
| PLKTN17        | 26568          | NEMA Type 12      | EasySwap       | 19in    | 12in    | 1.5in  |
| PLKTN28        | 26505          | NEMA Type 12      | EasySwap       | 33.25in | 12.25in | 1.5in  |
| PLM13N16       | 36414          | NEMA Type 12      | EasySwap       | 17.65in | 14.25in | 2.62in |
| PLM13N17       | 26556          | NEMA Type 12      | EasySwap       | 17.65in | 14.25in | 1.5in  |
| PLM28G28       | 26294          | NEMA Type 12      | EasySwap       | 28.5in  | 17in    | 1.5in  |
| PLM28N17       | 26557          | NEMA Type 12      | EasySwap       | 28.5in  | 17in    | 1.5in  |
| PLM33N28       | 26296          | NEMA Type 12      | EasySwap       | 34.31in | 12in    | 1.5in  |
| PLM36N36       | 26297          | NEMA Type 12      | EasySwap       | 38.75in | 15in    | 1.5in  |
| PLM52G52       | 26298          | NEMA Type 12      | EasySwap       | 52.56in | 17.03in | 1.5in  |
| PLPN36         | 26537          | NEMA Type 12      | EasySwap       | 36.5in  | 12in    | 1.5in  |
| PLR1N17        | 26066          | NEMA Type 12      | EasySwap       | 21.65in | 13in    | 1.5in  |
| PLR2G28        | 26504          | NEMA Type 12      | EasySwap       | 37.4in  | 16.97in | 1.5in  |

Table 2/2

| Catalog Number | Article Number | Protection Rating | Product Family | Height  | Width   | Depth |
|----------------|----------------|-------------------|----------------|---------|---------|-------|
| PLR2N17        | 26067          | NEMA Type 12      | EasySwap       | 21.65in | 12in    | 1.5in |
| PLRG28         | 21496          | NEMA Type 12      | EasySwap       | 37.4in  | 16.97in | 1.5in |
| PLRG52         | 19862          | NEMA Type 12      | EasySwap       | 61.13in | 17.13in | 1.5in |
| PLRG57         | 26073          | NEMA Type 12      | EasySwap       | 61.13in | 20.88in | 1.5in |
| PLRN28         | 26068          | NEMA Type 12      | EasySwap       | 29in    | 11.5in  | 1.5in |
| PLRN36         | 26538          | NEMA Type 12      | EasySwap       | 38in    | 15.75in | 1.5in |
| PLT29G28       | 26295          | NEMA Type 12      | EasySwap       | 28.5in  | 17in    | 1.5in |

## ADDITIONAL PRODUCT DETAILS

To quickly identify the correct air conditioner and plenum download the spec sheet from the Downloads tab or download the Easy Swap app from Apple App or Google play stores

Please contact Customer Service for support in finding an appropriate cross for older HOFFMAN/Mclean models not shown above.

Prior to ordering, ensure Adaptor Plenum dimensions do not exceed available space on the enclosure mounting surface.

ISC is a registered trademark of ISC Sales, Inc.

Kooltronic is a registered trademark of Kooltronic, Inc.

Pfannenbergl is a registered trademark of Pfannenbergl Incorporated

Rittal is a registered trademark of Rittal Corporation

Adaptor Plenums for Rittal are not suitable for replacing partial-recessed or fully-recessed mounted air conditioners.

Thermal Edge is a registered trademark of Thermal Edge, Inc.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.