

Front/Rear Plinth Base, PFS

This stainless steel plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.



FEATURES

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PSS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each panel for added strength.

Material: AISI 304 / AISI 316L pre-grained stainless steel. Corners 2 mm and panels 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1x front plinth and 1x rear plinth with mounting accessories.

Mounting requirements: Add the side panels PSS for a complete plinth.

Finish: Brushed
Thickness: 16ga

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Material
PFS1120	PFS1120	3.94in	47.24in	2.36in	Free-Standing	Stainless Steel 304
PFS2120		7.87in	47.24in	2.36in	Free-Standing	Stainless Steel 304
PFS1080	PFS1080	3.94in	31.5in	2.36in	Free-Standing	Stainless Steel 304
PFS2080		7.87in	31.5in	2.36in	Free-Standing	Stainless Steel 304
PFS1060	PFS1060	3.94in	23.62in	2.36in	Free-Standing	Stainless Steel 304
PFS2060		7.87in	23.62in	2.36in	Free-Standing	Stainless Steel 304
PFS1100		3.94in	39.37in	2.36in	Free-Standing	Stainless Steel 304
PFS2100		7.87in	39.37in	2.36in	Free-Standing	Stainless Steel 304
PFS1060-316		3.94in	23.62in	2.36in	Free-Standing	Stainless Steel 316

Catalog Number	Article Number	Height	Width	Depth	Product Family	Material
PFS1080-316		3.94in	31.5in	2.36in	Free-Standing	Stainless Steel 316
PFS1100-316		3.94in	39.37in	2.36in	Free-Standing	Stainless Steel 316
PFS1120-316		3.94in	47.24in	2.36in	Free-Standing	Stainless Steel 316
PFS2060-316		7.87in	23.62in	2.36in	Free-Standing	Stainless Steel 316
PFS2080-316		7.87in	31.5in	2.36in	Free-Standing	Stainless Steel 316
PFS2100-316		7.87in	39.37in	2.36in	Free-Standing	Stainless Steel 316
PFS2120-316		7.87in	47.24in	2.36in	Free-Standing	Stainless Steel 316

ADDITIONAL PRODUCT DETAILS

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

