

Insulated Mounting Panel, AMI



This is an easy to machine mounting plate that will prevent undesired contact between electrical components and the enclosure.

FEATURES

Description: Insulated mounting plate for wall mounted enclosures. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Bakelite.

Pack quantity: 1 piece.

Material: Bakelite
Finish: Smooth
Color: Black
Thickness: 10ga

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI02020	AMI02020	7.87in	7.87in	0.16in	6.69 x 5.91in	Mild Steel
AMI02520	AMI02520	9.84in	7.87in	0.16in	8.66 x 5.91in	Mild Steel
AMI02525	AMI02525	9.84in	9.84in	0.16in	8.66 x 7.87in	Mild Steel
AMI03025	AMI03025	11.81in	9.84in	0.16in	10.63 x 7.87in	Mild Steel
AMI03030	AMI03030	11.81in	11.81in	0.16in	10.63 x 9.84in	Mild Steel
AMI03040		11.81in	15.75in	0.16in	10.63 x 13.78in	Mild Steel
AMI03525		13.78in	9.84in	0.16in	12.59 x 7.87in	Mild Steel
AMI04030	AMI04030	15.75in	11.81in	0.16in	14.57 x 9.84in	Mild Steel
AMI04040	AMI04040	15.75in	15.75in	0.16in	14.57 x 13.78in	Mild Steel
AMI04050		15.75in	19.69in	0.16in	14.57 x 17.72in	Mild Steel
AMI04060	AMI04060	15.75in	23.62in	0.16in	14.57 x 21.65in	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI05030	AMI05030	19.69in	11.81in	0.16in	18.5 x 9.84in	Mild Steel
AMI05040	AMI05040	19.69in	15.75in	0.16in	18.5 x 13.78in	Mild Steel
AMI05050	AMI05050	19.69in	19.69in	0.16in	18.5 x 17.72in	Mild Steel
AMI06040	AMI06040	23.62in	15.75in	0.16in	22.44 x 13.78in	Mild Steel
AMI06050	AMI06050	23.62in	19.69in	0.16in	22.44 x 17.72in	Mild Steel
AMI06060	AMI06060	23.62in	23.62in	0.16in	22.44 x 21.65in	Mild Steel
AMI06080	AMI06080	23.62in	31.49in	0.16in	22.44 x 29.53in	Mild Steel
AMI07050	AMI07050	27.56in	19.69in	0.16in	26.38 x 17.72in	Mild Steel
AMI08040		31.49in	15.75in	0.16in	30.31 x 13.78in	Mild Steel

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI08060	AMI08060	31.49in	23.62in	0.16in	30.31 x 21.65in	Mild Steel
AMI08080		31.49in	31.49in	0.16in	30.31 x 29.53in	Mild Steel
AMI10060	AMI10060	39.37in	23.62in	0.16in	38.19 x 21.65in	Mild Steel
AMI10080	AMI10080	39.37in	31.49in	0.16in	38.19 x 29.53in	Mild Steel
AMI12060		47.24in	23.62in	0.16in	46.06 x 21.65in	Mild Steel
AMI12080	AMI12080	47.24in	31.49in	0.16in	46.06 x 29.53in	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

