

Mounting Plate, MP

The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Mounting requirements: Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.



Material: Mild Steel
Finish: Galvanized
Thickness: 11ga

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Mounting Plate Width	Enclosure Material
MP1606	MP1606	63in	23.62in	0.96in	19.44in	Mild Steel
MP1608	MP1608	63in	31.5in	0.96in	27.32in	Mild Steel
MP1806 	MP1806	70.87in	23.62in	0.96in	19.44in	Mild Steel
MP1808	MP1808	70.87in	31.5in	0.96in	27.32in	Mild Steel
MP2006	MP2006	78.74in	23.62in	0.96in	19.44in	Mild Steel
MP2008	MP2008	78.74in	31.5in	0.96in	27.32in	Mild Steel
MP1212	MP1212	47.24in	47.24in	0.96in	43.07in	Mild Steel
MP1612	MP1612	63in	47.24in	0.96in	43.07in	Mild Steel
MP1812	MP1812	70.87in	47.24in	0.96in	43.07in	Mild Steel
MP1816	MP1816	70.87in	63in	0.96in	58.82in	Mild Steel
MP2012	MP2012	78.74in	47.24in	0.96in	43.07in	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Mounting Plate Width	Enclosure Material
MP2016	MP2016	78.74in	63in	0.96in	58.82in	Mild Steel
MP1206	MP1206	47.24in	23.62in	0.96in	19.44in	Mild Steel
MP1208	MP1208	47.24in	31.5in	0.96in	27.32in	Mild Steel
MP1406	MP1406	55.12in	23.62in	0.96in	19.44in	Mild Steel
MP1408	MP1408	55.12in	31.5in	0.96in	27.32in	Mild Steel
MP1610	MP1610	63in	39.37in	0.96in	35.2in	Mild Steel
MP1810	MP1810	70.87in	39.37in	0.96in	35.2in	Mild Steel
MP2010	MP2010	78.74in	39.37in	0.96in	35.2in	Mild Steel
MP2210	MP2210	86.61in	39.37in	0.96in	35.2in	Mild Steel

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Mounting Plate Width	Enclosure Material
MP2212	MP2212	86.61in	47.24in	0.96in	43.07in	Mild Steel
MP1804	MP1804	70.87in	15.75in	0.96in	11.57in	Mild Steel
MP1805	MP1805	70.87in	19.69in	0.96in	15.51in	Mild Steel
MP2004	MP2004	78.74in	15.75in	0.96in	11.57in	Mild Steel
MP2005	MP2005	78.74in	19.69in	0.96in	15.51in	Mild Steel
MP2206	MP2206	86.61in	23.62in	0.96in	19.44in	Mild Steel
MP2208	MP2208	86.61in	31.5in	0.96in	27.32in	Mild Steel
MP1410	MP1410	55.12in	39.37in	0.96in	35.2in	Mild Steel
MP1412	MP1412	55.12in	47.24in	0.96in	43.07in	Mild Steel
MP2014	MP2014	74.57in	50.95in	0.96in	50.95in	Mild Steel
MP1818	MP1818	70.87in	70.87in	0.96in	66.7in	Mild Steel
MP2018	MP2018	78.74in	70.87in	0.96in	66.7in	Mild Steel

ADDITIONAL PRODUCT DETAILS

Note: for 1600 mm width, the mounting plate is delivered as two 800 mm width mounting plates and one filler plate.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

