

Partial Panels For Floor Standing Enclosures, DPP



Partial panels allow for many different, easily accessible, configurations of separate compartments within the enclosure. The panels are secured with screws, which ensures that it can only be removed by service personnel, to improve the operators safety.

FEATURES

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CDHK when no door is required.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 54.

Pack quantity: 1 panel with mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

Material:	Mild Steel
Finish:	Powder Coated
Color:	Light Gray
Color Code:	RAL 7035
Thickness:	0.07in

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPP01004R5	3.94in	15.75in	0.67in	Free-Standing	Mild Steel

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPP01006R5	3.94in	23.62in	0.67in	Free-Standing	Mild Steel
DPP01008R5	3.94in	31.5in	0.67in	Free-Standing	Mild Steel
DPP01504R5	5.91in	15.75in	0.67in	Free-Standing	Mild Steel
DPP01506R5	5.91in	23.62in	0.67in	Free-Standing	Mild Steel
DPP01508R5	5.91in	31.5in	0.67in	Free-Standing	Mild Steel
DPP02004R5	7.87in	15.75in	0.67in	Free-Standing	Mild Steel
DPP02006R5	7.87in	23.62in	0.67in	Free-Standing	Mild Steel
DPP02008R5	7.87in	31.5in	0.67in	Free-Standing	Mild Steel
DPP02504R5	9.84in	15.75in	0.67in	Free-Standing	Mild Steel
DPP02506R5	9.84in	23.62in	0.67in	Free-Standing	Mild Steel
DPP02508R5	9.84in	31.5in	0.67in	Free-Standing	Mild Steel
DPP03004R5	11.81in	15.75in	0.67in	Free-Standing	Mild Steel
DPP03006R5	11.81in	23.62in	0.67in	Free-Standing	Mild Steel
DPP03008R5	11.81in	31.5in	0.67in	Free-Standing	Mild Steel
DPP04004R5	15.75in	15.75in	0.67in	Free-Standing	Mild Steel
DPP04006R5	15.75in	23.62in	0.67in	Free-Standing	Mild Steel
DPP04008R5	15.75in	31.5in	0.67in	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.