

Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

Material:	Mild Steel
Finish:	Powder Coated
Color:	Light Gray
Color Code:	RAL 7035
Thickness:	14ga

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Height	Width	Depth	Door Type	Product Family
DN1106R5		42.6in	23.35in	0.66in	Plain	Free-Standing

Catalog Number	Article Number	Height	Width	Depth	Door Type	Product Family
DN1206LR5		46.54in	23.35in	0.66in	Left Door	Free-Standing
DN1206R5		46.54in	23.35in	0.66in	Plain	Free-Standing
DN1206RR5		46.54in	23.35in	0.66in	Right Door	Free-Standing
DN1208R5		46.54in	31.22in	0.66in	Plain	Free-Standing
DN1405LR5		54.41in	19.41in	0.66in	Left Door	Free-Standing
DN1405RR5		54.41in	19.41in	0.66in	Right Door	Free-Standing
DN1406LR5		54.41in	23.35in	0.66in	Left Door	Free-Standing
DN1406R5	DN1406R5	54.41in	23.35in	0.66in	Plain	Free-Standing
DN1406RR5		54.41in	31.22in	0.66in	Right Door	Free-Standing
DN1408R5	DN1408R5	54.41in	31.22in	0.66in	Plain	Free-Standing
DN1606LR5	DN1606LR5	62.28in	23.35in	0.66in	Left Door	Free-Standing
DN1606R5	DN1606R5	62.28in	23.35in	0.66in	Plain	Free-Standing
DN1606RR5	DN1606RR5	62.28in	23.35in	0.66in	Right Door	Free-Standing
DN1608R5	DN1608R5	62.28in	31.22in	0.66in	Plain	Free-Standing
DN1610R5	DN1610R5	62.28in	39.09in	0.66in	Plain	Free-Standing
DN1804LR5	DN1804LR5	70.16in	15.47in	0.66in	Left Door	Free-Standing
DN1804RR5	DN1804RR5	70.16in	15.47in	0.66in	Right Door	Free-Standing
DN1805LR5	DN1805LR5	70.16in	19.41in	0.66in	Left Door	Free-Standing
DN1805R5	DN1805R5	70.16in	19.41in	0.66in	Plain	Free-Standing

Table 2/3

Catalog Number	Article Number	Height	Width	Depth	Door Type	Product Family
DN1805RR5	DN1805RR5	70.16in	19.41in	0.66in	Right Door	Free-Standing
DN1806LR5	DN1806LR5	70.16in	23.35in	0.66in	Left Door	Free-Standing
DN1806R5	DN1806R5	70.16in	23.35in	0.66in	Plain	Free-Standing
DN1806RR5	DN1806RR5	70.16in	23.35in	0.66in	Right Door	Free-Standing
DN1808LR5	DN1808LR5	70.16in	31.22in	0.66in	Left Door	Free-Standing
DN1808R5	DN1808R5	70.16in	31.22in	0.66in	Plain	Free-Standing
DN1808RR5	DN1808RR5	70.16in	31.22in	0.66in	Right Door	Free-Standing
DN1810R5	DN1810R5	70.16in	39.09in	0.66in	Plain	Free-Standing
DN2004LR5	DN2004LR5	78.03in	15.47in	0.66in	Left Door	Free-Standing
DN2004RR5	DN2004RR5	78.03in	15.47in	0.66in	Right Door	Free-Standing
DN2005LR5	DN2005LR5	78.03in	19.41in	0.66in	Left Door	Free-Standing
DN2005R5	DN2005R5	78.03in	19.41in	0.66in	Plain	Free-Standing
DN2005RR5	DN2005RR5	78.03in	19.41in	0.66in	Right Door	Free-Standing
DN2006LR5	DN2006LR5	78.03in	23.35in	0.66in	Left Door	Free-Standing
DN2006R5	DN2006R5	78.03in	23.35in	0.66in	Plain	Free-Standing

Catalog Number	Article Number	Height	Width	Depth	Door Type	Product Family
DN2006RR5	DN2006RR5	78.03in	23.35in	0.66in	Right Door	Free-Standing
DN2008LR5	DN2008LR5	78.03in	31.22in	0.66in	Left Door	Free-Standing
DN2008R5	DN2008R5	78.03in	31.22in	0.66in	Plain	Free-Standing
DN2008RR5	DN2008RR5	78.03in	31.22in	0.66in	Right Door	Free-Standing
DN2010R5	DN2010R5	78.03in	39.09in	0.66in	Plain	Free-Standing

Table 3/3

Catalog Number	Article Number	Height	Width	Depth	Door Type	Product Family
DN2205LR5	DN2205LR5	85.91in	19.41in	0.66in	Left Door	Free-Standing
DN2205RR5	DN2205RR5	85.91in	19.41in	0.66in	Right Door	Free-Standing
DN2206LR5	DN2206LR5	85.91in	23.35in	0.66in	Left Door	Free-Standing
DN2206R5	DN2206R5	85.91in	23.35in	0.66in	Plain	Free-Standing
DN2206RR5	DN2206RR5	85.91in	23.35in	0.66in	Right Door	Free-Standing
DN2208R5	DN2208R5	85.91in	31.22in	0.66in	Plain	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

