

Straight Section Lay-in Painted Galvanized Hinged-Cover

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs.

FEATURES

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs



Material: Mild Steel
Finish: Galvanized; Powder Coated
Color: Gray
Color Code: ANSI 61

SPECIFICATIONS

Catalog Number	Article Number	Type	Height	Width	Depth	Thickness
F44T3R12	43489	Straight Section	4in	4in	12in	16ga
F44T3R120	43529	Straight Section	4in	4in	120in	16ga
F44T3R60	43509	Straight Section	4in	4in	60in	16ga
F66T3R12	43639	Straight Section	6in	6in	12in	16ga
F66T3R120	43679	Straight Section	6in	6in	120in	16ga
F66T3R60	43659	Straight Section	6in	6in	60in	16ga
F88T3R12	43799	Straight Section	8in	8in	12in	14ga
F88T3R120	43839	Straight Section	8in	8in	120in	14ga
F88T3R60	43819	Straight Section	8in	8in	60in	14ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.