

Universal U-Connector



U-Connectors are used to rigidly join lay-in wireway straight sections in series, as well as straight sections to fittings. The U-connector top swings aside to retain the lay-in feature of the wireway solution.

FEATURES

U-Connectors are used to rigidly join lay-in wireway straight sections in series, as well as straight sections to fittings

Top swings aside to retain the lay-in feature

U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates, or reducers

F44GUC and F66GUC designed to accept new Snap Connect Wireway for ease-of-installation; backwards compatible with legacy wireway design

Material: Mild Steel
Finish: Powder Coated
Color: Gray
Color Code: ANSI 61

SPECIFICATIONS

Catalog Number	Article Number	Type	Height	Width	Depth	Thickness
F1010GUC	46390	U-Connector	10in	2.5in		14ga
F1212GUC 	51940	U-Connector	12in	2.5in	2in	14ga
F22GUC	52100	U-Connector	2.5in	2.5in		16ga
F33GUC	15494	U-Connector	3in	2.5in		16ga
F44GUC 	52260	U-Connector	4in	2.5in	1.38in	16ga
F66GUC 	52430	U-Connector	6in	2.5in	1.38in	16ga
F88GUC 	52690	U-Connector	8in	2.5in	2in	14ga

ADDITIONAL PRODUCT DETAILS

Note: with presence of extruded holes, electric drivers recommended to secure fasteners

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.