


# Assembly Parts for Rugged Components



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

## FEATURES

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

**Product Family:** EuropacPRO  
**Product Type:** Assembly Kit



## SPECIFICATIONS

| Catalog Number | Type              | Package Quantity | Thread Size | Finish      | Material        | Works With |
|----------------|-------------------|------------------|-------------|-------------|-----------------|------------|
| 24566-100      | Countersunk Screw | 100              | M4          |             | Stainless Steel | Subracks   |
| 24566-101      | Countersunk Screw | 100              | M4          |             | Stainless Steel | Subracks   |
| 24560-140      | Square Nut        | 100              |             | Zinc Plated | Steel           | Subracks   |
| 24566-102      | Panhead Screw     | 100              | M4          |             | Stainless Steel | Subracks   |
| 24566-103      | Panhead Screw     | 100              | M4          |             | Stainless Steel | Subracks   |
| 24566-104      | Panhead Screw     | 100              | M4          |             | Stainless Steel | Subracks   |
| 24566-105      | Countersunk Screw | 100              | M4          |             | Stainless Steel | Subracks   |
| 24566-106      | Countersunk Screw | 100              | M4          |             | Stainless Steel | Subracks   |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

