

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

EMC Shielding:	No
Finish:	Anodized; Passivated
Material:	Aluminum
Product Type:	Subrack/Chassis



SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Package Quantity	Depth	For Mounting	Gasket Type	Handle Included
24563-191	3U	1	6.89in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-192	3U	1	9.25in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-193	3U	1	11.61in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-194	3U	1	13.98in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-491	6U	1	6.89in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-492	6U	1	9.25in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-493	6U	1	11.61in	DIN Connector	Stainless Steel EMC (retrofittable)	No
24563-494	6U	1	13.98in	DIN Connector	Stainless Steel EMC (retrofittable)	No

Table 2/2

Catalog Number	Mounting	Complies With	Rack Width
24563-191	Rack	IEC 60297-3-103	84HP
24563-192	Rack	IEC 60297-3-103	84HP
24563-193	Rack	IEC 60297-3-103	84HP
24563-194	Rack	IEC 60297-3-103	84HP
24563-491	Rack	IEC 60297-3-103	84HP
24563-492	Rack	IEC 60297-3-103	84HP
24563-493	Rack	IEC 60297-3-103	84HP
24563-494	Rack	IEC 60297-3-103	84HP

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

