


Grub Screw



Zero external envelope. Enables axial or radial positioning rather than clamping. Ideal for torque transmission.

FEATURES

- For mounting threaded insert and perforated strip at horizontal rail
- Slotted head requires flat-bladed screwdriver that enhances rotational leverage and simplify the installation process for fasteners
- Torx imprint bears greater torque
- The Torx star-shaped head prevents cam-out

Product Type: Screw
Type: Grub Screw



SPECIFICATIONS

Catalog Number	Package Quantity	Thread Size	Finish	Material	Product Family	Works With	Certifications
21100-276	100	M2.5	Nickel Plated	Steel	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Subracks, Cases, Chassis	RoHS
21100-646	100	M3	Nickel Plated	Steel	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Subracks, Cases, Chassis	RoHS
21102-980	100	M2.5		Stainless Steel		Subracks, Cases, Chassis	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.