

# B18 Combination Box/Conduit Hanger



The nVent CADDY B18 Combination Box/Conduit Hanger presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.

### FEATURES

- Scoreline breakaway feature can be easily modified by hand while maintaining UL listing
- Eliminates need for offset bending conduit
- Designed to be versatile and reusable
- Labor and time savings due to built-in first means of support
- NEC® & CEC compliant




### SPECIFICATIONS

| Table 1/2      |                     |                                   |                     |                |           |                |
|----------------|---------------------|-----------------------------------|---------------------|----------------|-----------|----------------|
| Catalog Number | Material            | Finish                            | Outer Diameter (OD) | Hole Size (HS) | Hole Type | Screw Included |
| 812MB18A       | Steel, Spring Steel | Pregalvanized, nVent CADDY Armour | 18 - 30 mm          | 6.4 mm         | Plain     | No             |

| Table 2/2      |            |           |
|----------------|------------|-----------|
| Catalog Number | Length (L) | Width (W) |
| 812MB18A       | 457.2mm    | 53.34 mm  |

### ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

