

107 Wraparound Strap for CPVC Pipe

FEATURES

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screw



Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B
1070075EG	597816	20	26.9 mm	5.8 mm	31.8 mm	60.3 mm
1070100EG	597817	25	33.7 mm	5.8 mm	36.5 mm	68.3 mm
1070125EG	597818	32	42.2 mm	5.8 mm	41.3 mm	77.8 mm
1070150EG	597819	40	48.3 mm	5.8 mm	44.5 mm	84.1 mm
1070200EG	597821	50	60.3 mm	5.8 mm	47.6 mm	93.7 mm

Table 2/2

Catalog Number	Article Number	C	Hanger Spacing
1070075EG	597816	30.2 mm	1.65 m Max
1070100EG	597817	30.2 mm	1.8 m Max
1070125EG	597818	30.2 mm	1.95 m Max
1070150EG	597819	30.2 mm	2.1 m Max
1070200EG	597821	30.2 mm	2.4 m Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

