


PEMSA Wire Basket Tray Center Support



FEATURES

Ideal for tray widths up to 200mm

Side load access for cable installation


IEC 61537 load rating and earthing compliant

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Article Number	Color	Length (L)	Width (W)	Height (H)	Hole Size (HS)	Certifications
WBTCTSPRTM10	820420		59mm	35 mm	5 mm	8 - 10 mm	CE, CADDY EU WBT QC, ANOR EU WTB EG S4 BG
WBTCTSPRTM10BG	820421	Black	59mm	35 mm	5 mm	8 - 10 mm	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT QC
WBTCTSPRTM6	820400		59mm	35 mm	5 mm	6 mm	CE, CADDY EU WBT QC



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

