

Saddle Washer



FEATURES

U-shaped wrap around washer



SPECIFICATIONS

Catalog Number	Article Number	Material	Finish	Hole Size (HS)	Thickness (T)	A	B
PLN10	589930	Steel	Electrogalvanized	10.5 mm	3 mm	42 mm	30 mm
PLN11S6	589928	Stainless Steel 316 (EN 1.4401)		11 mm	3 mm	42 mm	50 mm
PLN13	589940	Steel	Electrogalvanized	13 mm	3 mm	42 mm	30 mm
PLN13HD	589949	Steel	Hot-Dip Galvanized	13 mm	3 mm	42 mm	30 mm
PLN8	589925	Steel	Electrogalvanized	8.4 mm	3 mm	42 mm	30 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

