


Bisel para FMC Mezzanine Front Panel Cutouts, VITA 57,1



NÚMERO DE CATÁLOGO

20835-849

Un bisel de FMC se ajusta en los recortes del panel frontal del entresuelo de FMC, kit de 10 biseles de FMC.

CARACTERÍSTICAS

El bisel de FMC se ajusta en los recortes del panel frontal del entresuelo de FMC

La cubierta de FMC se puede proteger opcionalmente con junta tórica conductora, por favor pida esto por separado

Material, extrusión Al (anodizado, conductor superficial)



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Panel frontal

Tipo: Mezzanine Panel frontal

Tipo de accesorio: Panel frontal

Montaje: Me quedé

Apantallamiento EMC: No (Retrofitable)

Tipo de junta: Anillo tórico EMC

Material: Aluminio

Acabado frontal: Anodizado

Acabado trasero: Conductor

Bordes tratados: No

Altura: 58.45mm

Anchura: 12.8mm

Fondo: 2.5mm

De conformidad con: FMC Mezzanine; IEEE P1386

Cantidad del paquete: 10

Acabado: Anodizado

Peso neto: 0.1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Por favor, ordene EMC O-ring juntas por separado.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

