



	$\Delta R_{th}^{\text{K}} = \text{can be simulated}$		$\Delta R_{th}^{\text{K}} = \text{simulation not recommended}$		
light $\rightarrow$ R		-	+	+	+
heavy $\rightarrow$ R		+	+	+	+
light $\rightarrow$ L		+	+	+	+
heavy $\rightarrow$ L		+	+	-	-
light $\rightarrow$ R		+	+	+	+
heavy $\rightarrow$ R		+	+	+	+
light $\rightarrow$ L		+	+	+	+
heavy $\rightarrow$ L		+	+	+	+
light $\rightarrow$ R		+	+	+	+
heavy $\rightarrow$ R		+	+	+	+
light $\rightarrow$ L		+	+	+	+
heavy $\rightarrow$ L		+	+	+	+

34566-240

CARACTERÍSTICAS

Extrusión de aluminio, acabado anodizado, superficie de contacto conductora, con marcas HP



Peso bruto: 0.118kg

Sin rosca M4 al frente, sin impresión y sin muesca para soporte de 19".

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

