

Backplane VPX, 3 U, 5 ranuras, Full-Mesh, sin RTM

NÚMERO DE CATÁLOGO

23001-812

El backplane nVent SCHROFF VPX tiene una excelente integridad de señal para las tasas de transferencia de datos más altas.

CARACTERÍSTICAS


De conformidad con: VITA 46,0 VPX estándar básico; VITA 46,3 Serial RapidIO en VPX; VITA 46,4 PCI Express en el conector de tela VPX; VITA 46,7 Ethernet en el conector de tela VPX; VITA 46,11 System Management para VPX

Interruptor DIP para ajustes de ranura del sistema

Conexiones JTAG

Conectores auxiliares bloqueables y conectores de sentido

Pernos de alimentación M4 para fuente de alimentación, máx. 22 A por ranura para cada voltaje



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Plano trasero

Número de ranuras: 5

Altura del rack: 3U

Tipo de panel posterior: VPX full-mesh

Ancho de ranura: 4HP

Tipo de conector: MULTIGIG

Tipo de conector de alimentación: Powerstuds M4

Tipo de conector de servicios: Microfit, 8 pines

Anchura: 120.67mm

Peso neto: 0.352kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Otros backplanes VPX y diseños personalizados de backplane VPX bajo petición.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

