

# Microinterruptor de unidad enchufable para IEL, manija IET con cable y enchufe

## NÚMERO DE CATÁLOGO

**20817-606**

Micro Switch para IEL o IET mango. El micro interruptor se ajusta también a las versiones offset del mango.

## CARACTERÍSTICAS

PLÁSTICO, PC, UL 94 V-0

Conectores de acoplamiento adecuados no incluidos en el volumen de suministro


Max. Corriente conmutada 50 mA

Vida electora  $\geq 20.000$  ciclos de conmutación

Mech. La vida  $\geq 20.000$  ciclos de conmutación

Molex conector de carcasa

Molex crimp contacto y clip de fijación



## ATRIBUTOS DEL PRODUCTO

Tipo de producto: Conmutador

Compatible con: Paneles frontales

Material: Policarbonato

Cantidad del paquete: 10

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## DETALLES ADICIONALES DEL PRODUCTO

Conector de acoplamiento no incluido en la entrega. Conectores de acoplamiento de Molex por ejemplo 53261-0319, 53048-0310, 53047-0310, 53398-0319, 51047-0300.

**ADVERTENCIA**

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

