

Wire Basket Tray L Bracket



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

CARACTERÍSTICAS

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice


Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs

Material: Acero
Acabado: Electrogalvanizado



ESPECIFICACIONES

Número de catálogo	Color	Altura (H)	Anchura (W)	Longitud (L)	Tamaño de taladro (HS)	Peso por unidad
WBTLBRKT12		127 mm	41.4 mm	350.52mm	7.16 mm	0.712 kg
WBTLBRKT12BA	Negro	127 mm	41.4 mm	198.12mm	7.16 mm	0.712 kg
WBTLBRKT4		127 mm	41.4 mm	96.52mm	7.16 mm	0.395 kg
WBTLBRKT4BA	Negro	127 mm	41.4 mm	452.12mm	7.16 mm	0.395 kg
WBTLBRKT6		127 mm	41.4 mm	452.12mm	7.16 mm	0.476 kg
WBTLBRKT6BA	Negro	127 mm	41.4 mm	502.92mm	7.16 mm	0.476 kg
WBTLBRKT8		127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg
WBTLBRKT8BA	Negro	127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500

