



Unidad de control de velocidad de ventilador (Kit)



NÚMERO DE CATÁLOGO

20118-900

Adecuado para todos los ventiladores de CA y unidades de ventilador (hasta 300 W) con conector IEC 60320 C13 y C14 (plug & play).

Por favor ordene el cable de entrada actual / cable de red por separado

CARACTERÍSTICAS

El sensor externo se puede configurar en el punto de medición deseado

Salida de colector abierto (parametrizable) - Salida de alarma (activa/pasiva) - Ventiladores DC (salida PWM) - Pantalla remota (a través de pantalla digital opcional con panel frontal)

Montajes en el carril de apoyo proporcionado

Apto para todos los ventiladores y unidades de ventiladores de CA, EC y EC (hasta 300 W) con IEC 60320, conectores IEC C14 y C13

Ajuste sencillo de la temperatura del interruptor (con perilla y pantalla digital)

El cable de entrada actual / el cable de la cadena se puede elegir según el requisito del proyecto: SCHUKO-UTE / IEC / BS



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Módulo de control de ventilador

Compatible con: Varistar CP

Material: De plástico

Peso neto: 0.588kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

