

Unidad de control para LHX+ 5 KW y 10 KW

NÚMERO DE CATÁLOGO

23130-668



La Unidad de Control enriquece el LHX+. Se conecta a los sensores LHX+ y a la válvula de refrigerante motorizada 23130-607. Esto permite que el enfriador controle el flujo de aire refrigerante basado en un punto de ajuste de temperatura de aire refrigerado (suministro). Proporciona funcionalidad avanzada de monitoreo remoto y varias características de configuración.

CARACTERÍSTICAS

Control de flujo de refrigerante basado en el punto de ajuste de temperatura de aire enfriado (suministro). Más características de control con el paquete de control de agua

Unidad de control separada, compacta de 19" Sin cables sueltos en la sección superior del gabinete

Conexiones de sensor plug & play claramente marcadas

ATRIBUTOS DEL PRODUCTO

Altura: 88mm

Fondo: 220mm

Compatible con: Varistar; Varistar CP

Cantidad del paquete: 1

Color: Gris negro

Código de color: RAL 7021

Acabado: Aluminio-Zinc plateado

Tensión de entrada de CA: 230V

Material: Acero

Familia de productos: Varistar CP

Tipo de producto: Unidad de Control

Altura del rack: 2U

Anchura: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Pantalla externa opcional.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

