

Seguridad en rack Plus, 3 U, 120 V CA, filtro EMC



NÚMERO DE CATÁLOGO

21272-002

CARACTERÍSTICAS

19", Unidad de distribución de energía de 3 U con función de parada de emergencia

Suministra alimentación de la red de CA a dispositivos eléctricos o electrónicos como un interruptor de alimentación central

120 V fase a entrada de red neutra

Salidas de CA con diferentes tipos de conectores, conmutadas por interruptor ON/OFF

Salidas de CA permanentes (Servicio)

Todas las salidas están protegidas por disyuntores

La función de parada de emergencia cumple con los requisitos de EN 60947-5-1 y EN 60204-1 y es a prueba de vandalismo

Se puede conectar un botón externo adicional de parada de emergencia al sistema

UL pendiente

ATRIBUTOS DEL PRODUCTO

Tipo de producto: Distribuidor de potencia

Compatible con: Varistar CP; Novastar

Función: Parada de emergencia

Tensión de entrada de CA: 120V

Número de fases: 1

Filtro EMC: Sí

Limitador de pico de corriente: Sí

Limitador de corriente de irrupción: No

Dispositivo de corriente residual: No

Tapa del disyuntor: No

Altura del rack: 3U

Tipo de toma de corriente: NEMA 5-15R.; NEMA 5-20R.

Tipo de accesorio: Accesorios de distribución de energía

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Para la configuración exacta de las características opcionales y la configuración de ejemplo, consulte la tabla de elementos entregados.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

