



	"B" can be combined		"A" combinations not recommended		
Slipstream 1/8"		-	+	+	slabbed kit suggested
Slipstream 3/8"		+	slabbed kit Suggested for ConcretePCI	slabbed kit Suggested for rebarbed construction	+
Slipstream 1/2"		slabbed kit Suggested	+	-	-
Horizontal (all)					
	<i>Slab panel</i>	<i>Slabbed 1/8"</i>	<i>Slabbed 3/8"</i>	<i>Slabbed 1/2"</i>	<i>Slabbed 3/8"</i>

34560-520

CARACTERÍSTICAS

Estándar donde las demandas mecánicas son altas (H-ST)

< 28 HP no impreso

ATRIBUTOS DEL PRODUCTO

Cantidad del paquete: 1

Longitud: 106.68mm

Familia de productos: EuropacPRO; RatiopacPRO; RatiopacPRO AIRE; CompacPRO; PropacPRO

Tipo: Pesado, ST

Compatible con: Subpistas; Casos



DETALLES ADICIONALES DEL PRODUCTO

La entrega es en paquete estándar múltiplos. El precio es por artículo individual.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

