

# Improved nVent CADDY Cat HP J-Hook with Pedestal Clamp



The Improved nVent CADDY Cat HP J-Hook with Pedestal Clamp is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Pedestal Clamp attachment. The Assembly simplifies cable management by offering quick installation to pedestals under raised floors.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

## CARACTERÍSTICAS

Listed for use with flexible conduit, cable or tubing

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, raised floors and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



## ESPECIFICACIONES

Table 1/2

| Número de catálogo | Número de artículo | Material | Acabado        | Diámetro | Zona                | Capacidad del cable, Cat 5e |
|--------------------|--------------------|----------|----------------|----------|---------------------|-----------------------------|
| CAT32HPCD1B        | 181227             | Acero    | Pregalvanizado | 50 mm    | 2561mm <sup>2</sup> | 90                          |
| CAT48HPCD1B        | 181228             | Acero    | Pregalvanizado | 75 mm    | 5974mm <sup>2</sup> | 200                         |
| CAT64HPCD1B        | 181229             | Acero    | Pregalvanizado | 100 mm   | 9987mm <sup>2</sup> | 330                         |

Table 2/2

| Número de catálogo | Número de artículo | Capacidad del cable, Cat 6 | Capacidad del cable, Cat 6A | Tamaño del pedestal                |
|--------------------|--------------------|----------------------------|-----------------------------|------------------------------------|
| CAT32HPCD1B        | 181227             | 60                         | 35                          | 19 mm Square, 22.2 - 28.5 mm Round |
| CAT48HPCD1B        | 181228             | 150                        | 80                          | 19 mm Square, 22.2 - 28.5 mm Round |
| CAT64HPCD1B        | 181229             | 220                        | 140                         | 19 mm Square, 22.2 - 28.5 mm Round |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### Norteamérica

+1.800.753.9221

Opción 1: Atención al cliente

Opción 2: Soporte técnico

### Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

### Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

### Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500

