

Asennuskiskot, CP



This mounting rail can be cut to size and is ideal when components are fixed with sliding nuts.

FEATURES

Description: Installation profile with and without 25 mm hole pattern. Add GLM sliding nuts for easy installation of components.

Material: Galvanized steel.

Pack quantity: 10 x 2 m.

Material: Mild Steel
Finish: Galvanized
Thickness: 1.5mm

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Holes Included
CP1020H	10mm	20mm	2000mm	Yes
CP1020U	10mm	20mm	2000mm	No
CP2020H	20mm	20mm	2000mm	Yes
CP2020U	20mm	20mm	2000mm	No
CP2040H	20mm	40mm	2000mm	Yes
CP2040U	20mm	40mm	2000mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.