

Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FONCTIONS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Matériau: Acier
Finition: Prégalvanisé;Polyuréthane



SPÉCIFICATIONS

Table 1/2

Référence catalogue	Couleur	Hauteur (H)	Largeur (W)	Longueur (L)	Taille de trou (HS)	Rayon (R)
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm
WBTT2X12BA	Noir	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm
WBTT2X12WH	Blanc	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm
WBTT2X16		50.8 mm	617.22 mm	812.8mm	19.05 mm	94.64mm
WBTT2X16BA	Noir	50.8 mm	617.22 mm	812.8mm	19.05 mm	94.64mm
WBTT2X16WH	Blanc	50.8 mm	617.22 mm	812.8mm	19.05 mm	94.64mm
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm

Référence catalogue	Couleur	Hauteur (H)	Largeur (W)	Longueur (L)	Taille de trou (HS)	Rayon (R)
WBTT2X18BA	Noir	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm
WBTT2X18WH	Blanc	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm
WBTT2X20BA	Noir	50.8 mm	716.28 mm	911.86mm	19.05 mm	94.64mm
WBTT2X20WH	Blanc	50.8 mm	716.28 mm	911.86mm	19.05 mm	94.64mm
WBTT2X24		50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm
WBTT2X24BA	Noir	50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm
WBTT2X24WH	Blanc	50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm
WBTT2X4BA	Noir	50.8 mm	317.5 mm	513.08mm		94.64mm
WBTT2X4WH	Blanc	50.8 mm	317.5 mm	513.08mm		94.64mm
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm
WBTT2X6BA	Noir	50.8 mm	365.76 mm	561.34mm		94.64mm
WBTT2X6WH	Blanc	50.8 mm	365.76 mm	561.34mm		94.64mm

Table 2/2

Référence catalogue	Couleur	Hauteur (H)	Largeur (W)	Longueur (L)	Taille de trou (HS)	Rayon (R)
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm
WBTT2X8BA	Noir	50.8 mm	416.56 mm	612.14mm		94.64mm
WBTT2X8WH	Blanc	50.8 mm	416.56 mm	612.14mm		94.64mm

Table 1/2

Référence catalogue	Poids unitaire	Certifications
WBTT2X12	2.722 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X12BA	2.722 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X12WH	2.722 kg	
WBTT2X16	3.629 kg	
WBTT2X16BA	3.629 kg	
WBTT2X16WH	3.629 kg	
WBTT2X18	4.536 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X18BA	4.536 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X18WH	4.536 kg	
WBTT2X20BA	5.897 kg	
WBTT2X20WH	5.897 kg	
WBTT2X24	7.257 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X24BA	7.257 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X24WH	7.257 kg	

Référence catalogue	Poids unitaire	Certifications
WBTT2X4	0.454 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X4BA	0.454 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X4WH	0.454 kg	
WBTT2X6	1.361 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X6BA	1.361 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X6WH	1.361 kg	

Table 2/2

Référence catalogue	Poids unitaire	Certifications
WBTT2X8	1.814 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X8BA	1.814 kg	CE, nVent CADDY Wire Basket Tray System
WBTT2X8WH	1.814 kg	

DIAGRAMMES

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500

