

Adaptateur de mât standard pour paratonnerre




FONCTIONS

Raccorde les paratonnerres classiques au Mât en acier inoxydable de la série ER2

Matériau: Cuivre

SPÉCIFICATIONS

Référence catalogue	Taille du filetage 1 (TS1)	Taille du filetage 2 (TS2)	Hauteur (H)	Poids unitaire
INTCPTADM16	1 1/16" UNC	M16	40.6 mm	0.1 kg
INTCPTADM58	1 1/16" UNC	5/8" UNC	40.6 mm	0.1 kg



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500

