

Rail Wallmount SRW, EN50125-3 certified

Railway ready EN50125-3 vibration tested pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications.



FONCTIONS

Finish: powder painting UV resistant

Body: Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting

Door: Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left opening with door stopper. Right opening doors available on request

Roof: Rain & Sun hood to protect against adverse weather conditions

Lock: Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking

Cable access: Gland plate on the bottom. Cut-outs can be requested based on project specific requirements

Protection: Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10

Internal accessories: Standard: Document Pocket A4; Optional: 19" uprights on the front, Mounting plate in the rear

External accessories: Optional: Lifting eyes, wall/pole mount kits

Additional information: For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration. The standard RWS enclosures are delivered with 2 pressure compensation breathers. One under the hood, one on the Gland plate. The pressure compensation breathers are also IP66.

Right opening doors available on request. Gland plate cutouts can be requested based on project specific requirements.

Optional: 19" uprights on the front, Mounting plate in the rear

SPÉCIFICATIONS

Table 1/2

Référence catalogue	Hauteur du rack	Hauteur	Largeur	Profondeur	Indice de protection	Couleur
SRW0604021	13U	600mm	400mm	210mm	IP66	Gris clair
SRW0606021	13U	600mm	600mm	210mm	IP66	Gris clair
SRW0606030	13U	600mm	600mm	300mm	IP66	Gris clair
SRW0806021	17U	800mm	600mm	210mm	IP66	Gris clair
SRW0806030	17U	800mm	600mm	300mm	IP66	Gris clair

Table 2/2

Référence catalogue	Code couleur	Quantité par colis	Conformité	Finition	Matériau du bâti
SRW0604021	RAL 7035	1	EN 50125-3, CEI 62262, CEI 60529	Revêtement poudré	Acier inoxydable
SRW0606021	RAL 7035	1	EN 50125-3, CEI 62262, CEI 60529	Revêtement poudré	Acier inoxydable
SRW0606030	RAL 7035	1	EN 50125-3, CEI 62262, CEI 60529	Revêtement poudré	Acier inoxydable
SRW0806021	RAL 7035	1	EN 50125-3, CEI 62262, CEI 60529	Revêtement poudré	Acier inoxydable
SRW0806030	RAL 7035	1	EN 50125-3, CEI 62262, CEI 60529	Revêtement poudré	Acier inoxydable

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. Toutes les marques et tous les logos nVent sont la propriété ou sont sous licence de nVent Services GmbH ou de ses sociétés affiliées. Toutes les autres marques déposées sont la propriété de leurs détenteurs respectifs. nVent se réserve le droit de modifier les spécifications sans préavis.

Ce document est généré par le système.