


# Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FONCTIONS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Matériau:** Acier  
**Finition:** Prégalvanisé;Polyuréthane



## SPÉCIFICATIONS

Table 1/2


| Référence catalogue | Couleur | Hauteur (H) | Largeur (W) | Longueur (L) | Taille de trou (HS) | Rayon (R) |
|---------------------|---------|-------------|-------------|--------------|---------------------|-----------|
| WBTR902X12          |         | 50.8 mm     | 515.62 mm   | 515.62mm     | 19.05 mm            | 94.64mm   |
| WBTR902X12BA        | Noir    | 50.8 mm     | 515.62 mm   | 515.62mm     | 19.05 mm            | 94.64mm   |
| WBTR902X18          |         | 50.8 mm     | 665.734 mm  | 665.734mm    | 19.05 mm            | 94.64mm   |
| WBTR902X18BA        | Noir    | 50.8 mm     | 665.734 mm  | 665.734mm    | 19.05 mm            | 94.64mm   |
| WBTR902X24          |         | 50.8 mm     | 817.88 mm   | 817.88mm     | 19.05 mm            | 94.64mm   |
| WBTR902X24BA        | Noir    | 50.8 mm     | 817.88 mm   | 817.88mm     | 19.05 mm            | 94.64mm   |
| WBTR902X4           |         | 50.8 mm     | 317.7 mm    | 317.7mm      |                     | 94.64mm   |
| WBTR902X4BA         | Noir    | 50.8 mm     | 317.7 mm    | 317.7mm      |                     | 94.64mm   |
| WBTR902X6           |         | 50.8 mm     | 365.76 mm   | 365.76mm     |                     | 94.64mm   |

| Référence catalogue | Couleur | Hauteur (H) | Largeur (W) | Longueur (L) | Taille de trou (HS) | Rayon (R) |
|---------------------|---------|-------------|-------------|--------------|---------------------|-----------|
| WBTR902X6BA         | Noir    | 50.8 mm     | 365.76 mm   | 365.76mm     |                     | 94.64mm   |
| WBTR902X8           |         | 50.8 mm     | 416.56 mm   | 416.56mm     |                     | 94.64mm   |
| WBTR902X8BA         | Noir    | 50.8 mm     | 416.56 mm   | 416.56mm     |                     | 94.64mm   |

Table 2/2

| Référence catalogue | Poids unitaire | Certifications                                   |
|---------------------|----------------|--------------------------------------------------|
| WBTR902X12          | 1.814 kg       | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X12BA        | 1.814 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X18          | 3.175 kg       | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X18BA        | 3.175 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X24          | 4.99 kg        | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X24BA        | 4.99 kg        | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X4           | 0.454 kg       | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTR902X4BA         | 0.454 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X6           | 0.907 kg       | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X6BA         | 0.907 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X8           | 0.907 kg       | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X8BA         | 0.907 kg       | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMMES



## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Toutes les marques et tous les logos nVent sont la propriété ou sont sous licence de nVent Services GmbH ou de ses sociétés affiliées. Toutes les autres marques déposées sont la propriété de leurs détenteurs respectifs. nVent se réserve le droit de modifier les spécifications sans préavis.

Ce document est généré par le système.

