

34566-320

FONCTIONS

Profilé aluminium, finition anodisée, surface de contact conductrice, avec marquage en F



Combinations of horizontal rails and side panels

„+“ = can be combined „-“ = combination not recommended

Support 7.1		-	Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal
		Side panel 1.1 (flexible rail) for horizontal	+	Side panel 1.2 (rigid rail) for horizontal	+
Support 7.2		Side panel 1.1 (flexible rail) for horizontal	+	Side panel 1.2 (rigid rail) for horizontal	+
		Side panel 1.1 (flexible rail) for horizontal	+	Side panel 1.2 (rigid rail) for horizontal	+
Support 7.3		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
Support 7.4		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
Support 7.5		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
Support 7.6		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
Support 7.7		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-
Support 7.8		Side panel 1.1 (flexible rail) for horizontal	-	Side panel 1.2 (rigid rail) for horizontal	-

Horizontal rail 1:  Horizontal rail 2: 

Side panel 1.1:  Side panel 1.2: 

Support 7.1:  Support 7.2:  Support 7.3:  Support 7.4:  Support 7.5:  Support 7.6:  Support 7.7:  Support 7.8: 

ATTRIBUTS DU PRODUIT

Poids net: 0.03kg

nVent.com/SCHROFF | 1

s'ajoutent aux prix initialement proposés.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

