

# Clip per ripiano per scale nVent

The nVent CADDY Ladder Tray Clip makes attaching ladder trays to strut profiles quick and easy—featuring a single-piece design, ready for use out-of-the box with no loose hardware.

Offering two simple installation methods, the Ladder Tray Clip can be either installed on top of the strut or slid in from either end of the channel, increasing flexibility and giving contractors more options on the job. Designed for both indoor and outdoor installations, the hot-dip galvanized finish and hardware ensure longevity on rooftop, solar and trapeze projects.

## CARATTERISTICHE

Single-piece design with hardware pre-installed to reduce components

Simple and time-saving; just drop and twist the Ladder Tray Clip directly into the strut profile

Works on ladder tray with up to ½ in flange thickness

Hot-dip galvanized clamp and hardware for demanding environments

Integrated clamping teeth for superior holding strength and load ratings



## SPECIFICHE

Table 1/2

| Codice a catalogo | Numero articolo | Materiale | Finitura        | Spessore della flangia (FT) | A.    | B       |
|-------------------|-----------------|-----------|-----------------|-----------------------------|-------|---------|
| LTC               | 387715          | Acciaio   | Zincata a caldo | 13 mm Max                   | 49 mm | 38.1 mm |

Table 2/2

| Codice a catalogo | Numero articolo | Coppia (TQ) | Carico statico limite 1 (F1) | Carico statico limite 2 (F2) | Carico statico limite 3 (F3) |
|-------------------|-----------------|-------------|------------------------------|------------------------------|------------------------------|
| LTC               | 387715          | 41 N·m      | 2225N                        | 3100N                        | 10675N                       |



## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

### Nord America

+1.800.753.9221

Opzione 1 – Assistenza  
clienti

Opzione 2 – Assistenza  
tecnica

### Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

### Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

