

Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

CARATTERISTICHE

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit


Supported with 3/8 or 1/2 in threaded rod

Materiale: Acciaio
Finitura: Elettrozincato



SPECIFICHE

Codice a catalogo	Colore	Altezza (H)	Larghezza (W)	Lunghezza (L)	Dimensione del foro (HS)	Peso unitario
WBTCTSPRT12		193.55 mm	41.4 mm	292.176mm	15.75 mm	1.225 kg
WBTCTSPRT4		193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT4BA	Nero	193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT6		193.55 mm	41.4 mm	147.777mm	15.75 mm	0.816 kg
WBTCTSPRT8		193.55 mm	41.4 mm	190.551mm	15.75 mm	0.907 kg



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

