

Sensore a contatto digitale (ingresso) con alimentazione a 12 V per Guardian Management Gateway



CODICE A CATALOGO

21070-125

Sensori esterni che monitorano ingressi/uscite digitali con 2 connettori RJ45. È possibile collegare a margherita fino a 16 sensori tramite cavi patch e a una porta Guardian Management.

CARATTERISTICHE

Sensore esterno per Guardian Management Gateway

Una porta è in grado di monitorare fino a 16 sensori con una lunghezza totale del cavo di 40 metri

Se è collegato un sensore nVent SCHROFF Guardian, viene visualizzato nell'interfaccia Web con il tipo e il numero di serie

Alloggiamento in metallo

Facile montaggio

2 collegamenti RJ 45

Facile collegamento a margherita con cavo patch CAT6 (o schermatura superiore)

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sensore

Tipo: Contatto digitale

Funziona con: Gateway di gestione Guardian

Peso lordo: 0.097kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

