


Pannello frontale MicroTCA.4 (sopra MCH), formato intero singolo, schermato, SST



CODICE A CATALOGO

21850-103

Pannello frontale AdvancedTCA (acciaio inox) per guarnizioni tessili. I moduli di riempimento schermati vengono utilizzati per chiudere le fessure inutilizzate.

CARATTERISTICHE

Conforme alle specifiche MicroTCA.1 e MicroTCA.4

I moduli di riempimento schermati vengono utilizzati per chiudere le fessure inutilizzate

Può essere avvitato; è supportato sul binario di guida



ATTRIBUTI DEL PRODOTTO

Altezza: 84.68mm

Quantità nella confezione: 1

Tipo di accessorio: Pannello frontale

Montaggio: Anteriore a vite

Tipo di guarnizione: Tessuto

Finitura anteriore: Grezzo

Finitura posteriore: Grezzo

Profondità: 1mm

Schermatura EMC: Sì

Materiale: Acciaio inossidabile

Famiglia di prodotti: AdvancedMC

Tipo di prodotto: Pannello frontale

Tipo: Pannello frontale

Larghezza: 28.98mm

Peso netto: 0.055kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

