

Backplane VPX, 6 U, 5 slot, BKP6-DIS05-11.2.16-4 RTM

Obsoleto

CODICE A CATALOGO

23001-829

Il backplane nVent SCHROFF VPX ha un'eccellente integrità del segnale per velocità di trasferimento dati elevate.

CARATTERISTICHE


In conformità a: Base VITA 46,0 VPX standard; VITA 46,3 Serial RapidIO su VPX; VITA 46,4 PCI Express su connettore Fabric VPX; VITA 46,7 Ethernet su connettore Fabric VPX; Gestione del sistema VITA 46,11 per VPX

DIP switch per le impostazioni degli slot di sistema

Collegamenti JTAG

Connettori ausiliari bloccabili e di rilevamento

Prigionieri di alimentazione M4 per alimentazione, max. 22 A per slot per ogni tensione



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Backplane

Numero di scanalature: 5

Altezza del rack: 6U

Tipo di backplane: VPX, VITA 65

Larghezza asola: 5HP

Tipo di connettore: MultiGig

Tipo di connettore di alimentazione: Powerstuds M4

Tipo di connettore di servizio: Microfit, 8 pin

Larghezza: 135.55mm

Peso netto: 1.348kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Altri backplane VPX e backplane VPX personalizzati su richiesta.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

