



Guida orizzontale posteriore, tipo AB per i/o posteriore, con tacca, 84 CV



CODICE A CATALOGO

34579-040

Guida orizzontale in alluminio estruso di tipo AB (AB = supporto), per guide schede i/o posteriori, con superficie anodizzata e superficie di contatto conduttiva. Adatto per RatiopacPRO/-AIR ed EuropacPRO/-rugged).

CARATTERISTICHE

Per CompactPCI nell'area dell' i/o posteriore

Per l'espansione di 2 x 3 U, sono necessarie 2 guide orizzontali di tipo AB

Alluminio estruso, superficie anodizzata, superficie di contatto conduttiva, senza contrassegni HP

Combinations of horizontal rails and side panels

	Side panel A	Side panel B	Side panel C	Side panel D
Horizontal rail AB	+	+	+	+
Horizontal rail AC	+	+	+	+
Horizontal rail AD	+	+	+	+
Horizontal rail AE	+	+	+	+
Horizontal rail AF	+	+	+	+
Horizontal rail AG	+	+	+	+
Horizontal rail AH	+	+	+	+
Horizontal rail AI	+	+	+	+
Horizontal rail AJ	+	+	+	+
Horizontal rail AK	+	+	+	+
Horizontal rail AL	+	+	+	+
Horizontal rail AM	+	+	+	+
Horizontal rail AN	+	+	+	+
Horizontal rail AO	+	+	+	+
Horizontal rail AP	+	+	+	+
Horizontal rail AQ	+	+	+	+
Horizontal rail AR	+	+	+	+
Horizontal rail AS	+	+	+	+
Horizontal rail AT	+	+	+	+
Horizontal rail AU	+	+	+	+
Horizontal rail AV	+	+	+	+
Horizontal rail AW	+	+	+	+
Horizontal rail AX	+	+	+	+
Horizontal rail AY	+	+	+	+
Horizontal rail AZ	+	+	+	+

ATTRIBUTI DEL PRODOTTO

Larghezza rack: 84HP

Quantità nella confezione: 1

Finitura: Anodizzato

Lunghezza: 431.8mm

Materiale: Alluminio

Famiglia di prodotti: EuropacPRO

Tipo di prodotto: Guida orizzontale

Tipo: Tipo AB

Funziona con: Rack secondari

Peso netto: 0.073kg

Tipo di rotaia: Con intaglio

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

La consegna è in confezioni multiple standard. I prezzi si riferiscono a ciascun articolo.

Tenere presente che le consegne possono essere effettuate nei QSP indicati (ad esempio 5 pezzi, 10 pezzi, 50 pezzi, ecc.). Le quantità d'ordine diverse (ad esempio 2 pezzi) possono essere modificate con la quantità di consegna successiva possibile = quantità confezione standard.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

