


# Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## CARATTERISTICHE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Materiale:** Acciaio  
**Finitura:** Prezincato;Poliuretano



## SPECIFICHE

Table 1/2


| Codice a catalogo | Colore | Altezza (H) | Larghezza (W) | Lunghezza (L) | Dimensione del foro (HS) | Raggio (R) |
|-------------------|--------|-------------|---------------|---------------|--------------------------|------------|
| WBTR902X12        |        | 50.8 mm     | 515.62 mm     | 515.62mm      | 19.05 mm                 | 94.64mm    |
| WBTR902X12BA      | Nero   | 50.8 mm     | 515.62 mm     | 515.62mm      | 19.05 mm                 | 94.64mm    |
| WBTR902X18        |        | 50.8 mm     | 665.734 mm    | 665.734mm     | 19.05 mm                 | 94.64mm    |
| WBTR902X18BA      | Nero   | 50.8 mm     | 665.734 mm    | 665.734mm     | 19.05 mm                 | 94.64mm    |
| WBTR902X24        |        | 50.8 mm     | 817.88 mm     | 817.88mm      | 19.05 mm                 | 94.64mm    |
| WBTR902X24BA      | Nero   | 50.8 mm     | 817.88 mm     | 817.88mm      | 19.05 mm                 | 94.64mm    |
| WBTR902X4         |        | 50.8 mm     | 317.7 mm      | 317.7mm       |                          | 94.64mm    |
| WBTR902X4BA       | Nero   | 50.8 mm     | 317.7 mm      | 317.7mm       |                          | 94.64mm    |
| WBTR902X6         |        | 50.8 mm     | 365.76 mm     | 365.76mm      |                          | 94.64mm    |

| Codice a catalogo | Colore | Altezza (H) | Larghezza (W) | Lunghezza (L) | Dimensione del foro (HS) | Raggio (R) |
|-------------------|--------|-------------|---------------|---------------|--------------------------|------------|
| WBTR902X6BA       | Nero   | 50.8 mm     | 365.76 mm     | 365.76mm      |                          | 94.64mm    |
| WBTR902X8         |        | 50.8 mm     | 416.56 mm     | 416.56mm      |                          | 94.64mm    |
| WBTR902X8BA       | Nero   | 50.8 mm     | 416.56 mm     | 416.56mm      |                          | 94.64mm    |

Table 2/2

| Codice a catalogo | Peso unitario | Certificazioni                                   |
|-------------------|---------------|--------------------------------------------------|
| WBTR902X12        | 1.814 kg      | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X12BA      | 1.814 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X18        | 3.175 kg      | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X18BA      | 3.175 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X24        | 4.99 kg       | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X24BA      | 4.99 kg       | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X4         | 0.454 kg      | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTR902X4BA       | 0.454 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X6         | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X6BA       | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X8         | 0.907 kg      | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X8BA       | 0.907 kg      | CE, nVent CADDY Wire Basket Tray System          |

## SCHEMI



## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

#### **Nord America**

+1.800.753.9221

Opzione 1 – Assistenza  
clienti

Opzione 2 – Assistenza  
tecnica

#### **Europa**

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

#### **Europa**

Germania:

800 1890272

altri paesi:

+31 13 5835404

#### **APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

