

Raccordo a T preformato per vassoio per cavi WBT Performance



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

CARATTERISTICHE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Materiale: Acciaio
Finitura: Prezincato;Poliuretano



SPECIFICHE

Table 1/2

Codice a catalogo	Color e	Altezza (H)	Larghezza (W)	Lunghezza (L)	Dimensione del foro (HS)	Raggio (R)	Peso unitario
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X12BA	Nero	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X18BA	Nero	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X24		50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm	7.257 kg

Codice a catalogo	Color e	Altezza (H)	Larghezza (W)	Lunghezza (L)	Dimensione delforo (HS)	Raggio (R)	Peso unitario
WBTT2X24BA	Nero	50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X4BA	Nero	50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X6BA	Nero	50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT2X8BA	Nero	50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT6X6		152.39999999999999 8 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Nero	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Nero	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Nero	101.6 mm					

Table 2/2

Codice a catalogo	Color e	Altezza (H)	Larghezza (W)	Lunghezza (L)	Dimensione del foro (HS)	Raggio (R)	Peso unitario
WBTT4X4		101.6 mm					
WBTT4X4BA	Nero	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Nero	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Nero	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Nero	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Nero	152.4 mm					
WBTT6X36		152.4 mm					

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

