

Cat HP J-Hook Mod clip voor M4-M12 draadeind, 4,8 - 6,4mm draad



CATALOGUSNUMMER


CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

KENMERKEN

Assemblage zonder gereedschap

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



PRODUCTKENMERKEN

Artikelnummer: 186082


Afwerking: nVent CADDY Armour

Materiaal: Verenstaal

Staaftmaat (RS): M4;M6;M8;M10;M12

Draadgrootte: 4.8 - 6.4 mm

Statische belasting: 130N



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221
optie 1 – Klantenservice
optie 2 – Technische
ondersteuning

Europa

Nederland:
+31 800-0200135
Frankrijk:
+33 800 901 793

Europa

Duitsland:
800 1890272
andere landen:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

