

Wire Basket Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY Wire Basket Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

KENMERKEN

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY Wire Basket Tray Ground Splice and nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

Materiaal: Staal




SPECIFICATIES

Catalogusnummer	Afwerking	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Gewicht eenheid
WBTCLSPRT12	Elektrolytisch verzinkt		15.75 mm	41.4 mm	388.417m m	13.49 mm	0.499 kg
WBTCLSPRT12BA	Elektrolytisch verzinkt	Zwart	15.75 mm	41.4 mm	388.417m m	13.49 mm	0.499 kg
WBTCLSPRT18	Elektrolytisch verzinkt		15.75 mm	41.4 mm	538.226m m	13.49 mm	0.726 kg

Catalogusnummer	Afwerking	Kleur	Hoogte(H)	Breedte(W)	Lengte (L)	Gatgrootte (HS)	Gewicht eenheid
WBTCLSPRT18BA	Elektrolytisch verzinkt	Zwart	15.75 mm	41.4 mm	538.226m m	13.49 mm	0.726 kg
WBTCLSPRT24	Elektrolytisch verzinkt		15.75 mm	41.4 mm	688.442m m	13.49 mm	0.862 kg
WBTCLSPRT24BA	Elektrolytisch verzinkt	Zwart	15.75 mm	41.4 mm	688.442m m	13.49 mm	0.862 kg
WBTCLSPRT6	Voorgegalvaniseerd		15.75 mm	41.4 mm	238.404m m	13.49 mm	0.249 kg
WBTCLSPRT6BA	Voorgegalvaniseerd	Zwart	15.75 mm	41.4 mm	238.404m m	13.49 mm	0.249 kg
WBTCLSPRT8	Voorgegalvaniseerd		15.75 mm	41.4 mm	288.392m m	13.49 mm	0.363 kg
WBTCLSPRT8BA	Voorgegalvaniseerd	Zwart	15.75 mm	41.4 mm	288.392m m	13.49 mm	0.363 kg

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221

optie 1 – Klantenservice

optie 2 – Technische
ondersteuning

Europa

Nederland:

+31 800-0200135

Frankrijk:

+33 800 901 793

Europa

Duitsland:

800 1890272

andere landen:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

