

# Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

## KENMERKEN

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit


Supported with 3/8 or 1/2 in threaded rod

**Materiaal:** Staal  
**Afwerking:** Elektrolytisch verzinkt



## SPECIFICATIES

| Catalogusnummer | Kleur | Hoogte (H) | Breedte (W) | Lengte (L) | Gatgrootte (HS) | Gewicht eenheid |
|-----------------|-------|------------|-------------|------------|-----------------|-----------------|
| WBTCTSPRT12     |       | 193.55 mm  | 41.4 mm     | 292.176mm  | 15.75 mm        | 1.225 kg        |
| WBTCTSPRT4      |       | 193.55 mm  | 41.4 mm     | 105.156mm  | 15.75 mm        | 0.7 kg          |
| WBTCTSPRT4BA    | Zwart | 193.55 mm  | 41.4 mm     | 105.156mm  | 15.75 mm        | 0.7 kg          |
| WBTCTSPRT6      |       | 193.55 mm  | 41.4 mm     | 147.777mm  | 15.75 mm        | 0.816 kg        |
| WBTCTSPRT8      |       | 193.55 mm  | 41.4 mm     | 190.551mm  | 15.75 mm        | 0.907 kg        |



## WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

### Noord-Amerika

+1.800.753.9221  
optie 1 – Klantenservice  
optie 2 – Technische  
ondersteuning

### Europa

Nederland:  
+31 800-0200135  
Frankrijk:  
+33 800 901 793

### Europa

Duitsland:  
800 1890272  
andere landen:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

