

# Wire Basket Tray Drop Out



The nVent CADDY Wire Basket Tray Drop Out is a versatile solution for creating cable management exits in cable tray. By acting as a wire funnel, the Drop Out enables cables to easily drop vertically from the tray while ensuring proper support and protecting the bend radius at the exit point. The tool-free design allows installers to drop the component into place on the wire basket tray while the side prongs hold it firmly in place. Whether contractors are working with multi-tier assemblies or side-by-side configurations, the Drop Out offers an aesthetic and efficient way to manage cable transitions, without compromising on performance or accessibility.

## KENMERKEN

Designed for center cable tray dropouts

Conducive to creating both multi-tier tray and side-by-side assemblies

Easily cut to fit around the wire basket tray for retrograde cable installations

Ensures the natural bend radius of the cable is protected

Stackable for multiple adjoining dropouts


Reusable and tool-free—easy-to-install, easy-to-remove

**Materiaal:** ABS, UL-VO-classificatie

**Afwerking:** Voorgegalvaniseerd

## SPECIFICATIES

| Catalogusnummer | Hoogte (H) | Breedte (W) | Lengte (L) | Gewicht eenheid |
|-----------------|------------|-------------|------------|-----------------|
| WBTCBLDO        | 28.6 mm    | 58.74 mm    | 90.5mm     | 0.05 kg         |
| WBTCBLDO4       | 28.6 mm    | 109.3 mm    | 92.08mm    | 0.01 kg         |
| WBTCBLDO6       | 29.4 mm    | 158 mm      | 210.85mm   | 0.02 kg         |



## WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

### Noord-Amerika

+1.800.753.9221  
optie 1 – Klantenservice  
optie 2 – Technische  
ondersteuning

### Europa

Nederland:  
+31 800-0200135  
Frankrijk:  
+33 800 901 793

### Europa

Duitsland:  
800 1890272  
andere landen:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

